

IN-LINE PROBE HOLDERS

"PEA" - "PEB"

Data Sheet

FEATURES

- In-line and immersion probe-holders
- Easy assembling


SPECIFICATIONS

PEA in-line probe-holder

Electrodes	pH, ORP Ø 12
Max operating pressure	7 bar (3bar)
Max temperature	90°C (130°C)
Fittings	1/2"
Material	PVDF


PEB in-line probe-holder

Electrodes	pH, ORP Ø 12
Max operating pressure	7 bar (3bar)
Max temperature	90°C (130°C)
Fittings	3/4"
Material	PP



PEA/SN6 in-line probe-holder

Electrodes	pH, ORP, threading PG 13.5
Max operating pressure	7 bar
Max temperature	90°C
Fittings	1/2"
Material	PVDF




IN-LINE PROBE HOLDERS

"PEA" - "PEB"

Data Sheet

PEA / PEB EXPLODED VIEW



EXEMPLE:
PEA / PEB INSTALLATION
ON EPH PROBE

